



Lead-Free Solder Paste PF606-P214L

Rev. 2017/06/30 Ver. 02-01

BASIC OVERVIEW



SnAg3.0Cu0.5X Solder Paste Halide Free No Clean Low Voiding

APPLICATIONS

Universal Lead-Free SMD Solder Paste Wide Range of Applications and PCB designs

FEATURES

| Appearance | Gray paste | w/o visible | | | | | | |
|-------------------|---------------------------------------|-------------|------------|----------|-------|--------------------|--|--|
| Alloy Composition | Sn/Ag3.0/0 | Cu0.5/x | JIS-Z-3282 | | | | | |
| Melting Point | 217~219 °C | | | | | | | |
| Particle Size | (Type 3) | +45μm | < 1% | , - 20µm | < 10% | J-STD-005 | | |
| | (Type 4) | +38µm | < 1% | , - 20µm | < 10% | | | |
| | (Type 5) | +25μm | < 1% | , - 15µm | < 10% | | | |
| | | | | | | | | |
| Powder Shape | Spherical | | | | | | | |
| Flux Content | 13% ± 1.0 wt% | | | | | JIS-Z-3197, 8.1.2 | | |
| Viscosity | 100 ± 30 Pa.s (25±1°C, 10rpm, Malcom) | | | | | JIS-Z-3284 Annex 6 | | |
| Flux Type | ROL0 | | | | | J-STD-004A | | |

Alloy Detail Composition

| (Sn) | (Ag) | (Cu) | (Ni) | (Ge) | (Zn) | (AI) | (Sb) | (Fe) | (As) | (Bi) | (Cd) | (Au) | (In) | (Pb) |
|------|------|------|------|------|-------|-------|------|------|------|------|-------|------|------|------|
| DEM | 2.8~ | 0.3~ | 0~ | 0~ | 0.001 | 0.001 | 0.05 | 0.02 | 0.03 | 0.10 | 0.002 | 0.05 | 0.10 | 0.05 |
| REM. | 3.2 | 0.7 | 0.01 | 0.01 | MAX | MAX | MAX | MAX | MAX | MAX | MAX | MAX | MAX | MAX |

Patent No.: Japanese Patent No. 3296289, U.S Patent No. 6179935B1, Germany Patent No.19816671C2

(wt%)

Scan Code for Solder Paste Documents







Lead-Free Solder Paste PF606-P214L

Rev. 2017/06/30 Ver. 02-01


PERFORMANCE & RELIABILITY

| Copper Plate Corrosion Test | Pass | JIS-Z-3197, 8.4.1 |
|------------------------------|---------------|-----------------------|
| Spreading Test | > 70% | JIS-Z-3197, 8.3.1.1 |
| Halogen Content Test | ROL0 | BS EN14582 |
| Copper Mirror Test | Pass | IPC-TM-650, 2.3.32 |
| Viscosity Test (25°C,10 rpm) | 100 ± 30 Pa.s | JIS-Z-3284. Annex 6 |
| Tackiness Test (gf) | > 130 (8hr) | JIS-Z-3284. Annex 9 |
| Slump Test | Pass | JIS-Z-3284. Annex 7,8 |
| Solder Ball Test | Pass | JIS-Z-3284. Annex 11 |

| S.I.R. Test | A | Pass | IPC-TM-650, 2.6.3.3 |
|------------------------|----------|------|----------------------|
| Electro Migration Test | ♦ | Pass | IPC-TM-650, 2.6.14.1 |

▲ Test Conditions: 85 °C, 85% RH for 168hrs ◆ Test Conditions: 65°C, 88.5% RH for 596 hrs

RECOMMENDED REFLOW PROFILE



Ramp Up Rate (30-150°C): 1.0-3.0 °C/sec

Pre-heating Time (150-200°C): 30-120 sec

Time Period Above 220°C: >30 sec

Peak Temperature: 230-250 °C

Ramp Down Cooling Rate: 1.0-6.0 °C/sec

Note: The recommended reflow profile is provided as a guideline. Optimal profile may differ due to oven type, assembly layout or other process variables.





Lead-Free Solder Paste PF606-P214L

Rev. 2017/06/30 Ver. 02-01

STORAGE & HANDLING:

- Refrigerate the solder paste at 0-10°C helps prolong shelf life. Normal shelf life is 6 months from production date (sealed jars).
- Keep away of direct sunlight.
- Allow the paste to reach ambient temperature 22-28°C for 3-4 hrs. Do not heat to raise temperature abruptly.
- It is recommended to keep the environment at 22-28°C and RH 30-60%.
- It is recommended to finish fresh paste within 24 hrs.
- Before setup, continuously dispense until the paste has filled the needle insides and paste is flowing freely.
- Time/pressure dispensers should be set up with manufacturer's guidelines.
- After dispensing, it is suggested to place components to be mounted on the PCB and reflow within 4~6 hrs.
- To clean up printed circuit boards, it is suggested to use ethanol or isopropanol.

Note: For more information, please refer to solder paste application guideline sheet

HOW TO ORDER

PF606 - P214L - T3 - 500

Solder Alloy PF606 = SnAg3.0Cu0.5 Flux

Particle Size

 $T5 = 15-25\mu m$ 150 = syringe 150g

Weight / Packaging $P214L = ROL0 T3 = 20-45\mu m 30 = syringe 30g$

 $T4 = 20-38 \mu m$ 100 = syringe 100g

250 = plastic jar 250g

500 = plastic jar 500g

600 = small cartridge 600g

1200 = large cartridge 1200g

CARTRIDGE



SYRINGE

CONTACTS

Tel.: +49-152-5106-5427



support@nevo-solder.com



www.nevo-solder.com

NOTICE: Specifications are subject to change without notice. Contact NeVo® for the latest specifications. All statements, information and data given herein are believed to be accurate and reliable, but are presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements or suggestions concerning possible use of our product are made without responsibility or warranty that any such use is free of patent infringement and are not recommendations to infringe any patent. The user should not assume that all safety measures are indicated or that other measures are indicated or that measures may not be required. Specifications are typical and may not apply to all applications.

NeVo®, Škrobárenská 506/2, 617 00 BRNO, CZECH REPUBLIC